

# Fuse Accessory Selection Guide

Fuse	Size	PC Board Fuse Clip (Qty. 2)	PC Board Mount Holder	Panel Mount Holder	In-Line Fuse Holder	Fuse Block
ABC	1/4" x 1/4"	1A1907*	HBH-I / HBV-I	HTB* / HKP*	HRK / HHB / HFA*	S-8000*
AGA	1/4" x 5/8"	1A1907*	-	-	-	-
AGC	1/4" x 1/4"	1A1907*	HBH-I / HBV-I	HTB* / HKP*	HRK / HHB / HFA*	S-8000*
AGU	13/32" x 1 1/2"	1A3400*	-	HPG*	HEB*	BM6031PQ
AGW	1/4" x 7/8"	1A1907*	-	-	HRK / HHB / HFA*	-
AGX	1/4" x 1"	1A1907*	-	HJL	HRK / HHB / HFA*	3828-1
ATC	-	1A5600	-	-	HHD	-
ATM	-	1A5778	-	-	HHM	-
BAF	13/32" x 1 1/2"	1A3400*	-	HPG*	HEB*	BM6031PQ
BAN	13/32" x 1 1/2"	1A3400*	-	HPG*	HEB*	BM6031PQ
BBS	13/32" x 1 3/8"	1A3400*	-	HPS-L	HEH*	BM6031PQ
C519	5 x 15mm	1A3399*	-	-	HHT	-
C520	5 x 15mm	1A3399*	-	-	HHT	-
DCM	13/32" x 1 1/2"	1A3400*	-	HPG*	HEB*	BM6031PQ
FNA	13/32" x 1 1/2"	1A3400*	-	HPG*	HEB*	BM6031PQ
FNM	13/32" x 1 1/2"	1A3400*	-	HPG*	HEB*	BM6031PQ
FNQ	13/32" x 1 1/2"	1A3400*	-	HPG*	HEB*	BM6031PQ
FNQ-R	13/32" x 1 1/2"	1A3400*	-	HPG*	-	BC6031PQ
FWH	1/4" x 1/4"	1A1907*	-	-	-	-
GBA	1/4" x 1/4"	1A1907*	-	HLD	HRK / HHB / HFA*	S-8000*
GBB	1/4" x 1/4"	1A1907*	HBH-I / HBV-I	HTB* / HKP*	HRK / HHB / HFA*	S-8000*
GLD	1/4" x 1/4"	1A1907*	-	HLD	HRK / HHB / HFA*	S-8000*
GMA	5 x 20mm	1A3399*	HTC-45M / -50M	HTB* / HTC*	HHT	HTC-15M
GMC	5 x 20mm	1A3399*	HTC-45M / -50M	HTB* / HTC*	HHT	HTC-15M
GMD	5 x 20mm	1A3399*	HTC-45M / -50M	HTB* / HTC*	HHT	HTC-15M
KLM	13/32" x 1 1/2"	1A3400*	-	HPG*	HEB*	BM6031PQ
KTK	13/32" x 1 1/2"	1A3400*	-	HPG*	HEB*	BM6031PQ
KTK-R	13/32" x 1 1/2"	1A3400*	-	HPG*	-	BC6031PQ
KTQ	13/32" x 1 3/8"	1A3400*	-	HPS-L	HEH*	BM6031PQ
LP-CC	13/32" x 1 1/2"	1A3400*	-	HPG*	-	BC6031PQ
MDA	1/4" x 1/4"	1A1907*	HBH-I / HBV-I	HTB* / HKP*	HRK / HHB / HFA*	S-8000*
MDL	1/4" x 1/4"	1A1907*	HBH-I / HBV-I	HTB* / HKP*	HRK / HHB / HFA*	S-8000*
MDQ	1/4" x 1/4"	1A1907*	HBH-I / HBV-I	HTB* / HKP*	HRK / HHB / HFA*	S-8000*
MIC	13/32" x 1 1/2"	1A3400*	-	HPG*	HEB*	BM6031PQ
MIN	13/32" x 1 1/2"	1A3400*	-	HPG*	HEB*	BM6031PQ
PCB	-	-	PCS	-	-	-
PCD	-	-	PCS	-	-	-
S500 / GDB	5 x 20mm	1A3399*	HTC-45M / -50M	HTB* / HTC*	HHT	HTC-15M
S501 / GDA	5 x 20mm	1A3399*	HTC-45M / -50M	HTB* / HTC*	HHT	HTC-15M
S505	5 x 20mm	1A3399*	HTC-45M / -50M	HTB* / HTC*	HHT	HTC-15M
S506 / GDC	5 x 20mm	1A3399*	HTC-45M / -50M	HTB* / HTC*	HHT	HTC-15M
SC-1 to 15	13/32" x 1.31"	1A3400*	-	HPS-EE	HEG	BG3011PQ
SC-20	13/32" x 1.41"	1A3400*	-	HPS-JJ	HEH*	BG3021PQ
SC-25 to 30	13/32" x 1.62"	1A3400*	-	HPS-FF	HEC*	BG3031PQ
SC-35 to 60	13/32" x 2 1/4"	1A3400*	-	-	HEJ*	G30060-1CR
SR-5	-	-	PCS	-	-	-
SR-5F	-	-	PCS	-	-	-
SS-5	-	-	PCS	-	-	-
SS-5F	-	-	PCS	-	-	-
TDC10	1/4" x 1/4"	1A1907*	HTC-45M / -50M	HTB* / HKP*	HRK / HHB / HFA*	S-8000*
TDC11	1/4" x 1/4"	1A1907*	HTC-45M / -50M	HTB* / HKP*	HRK / HHB / HFA*	S-8000*
TDC180	1/4" x 1"	1A1907*	-	HJL	HRK / HHB / HFA*	3828-1

\* These are not complete catalog numbers, but part Series that contain variations in construction and/or materials to meet particular design needs/objectives. Consult the Cooper Bussmann catalog for full descriptions and complete catalog numbers.

# Quick Cross Reference

Littelfuse	Cooper Bussmann	Description
213	S506	5mm Fuses
215	S505	5mm Fuses
216	S501	5mm Fuses
217	S500	5mm Fuses
218	S506	5mm Fuses
220	C517	5mm Fuses
224	C518	5mm Fuses
225	C520	5mm Fuses
229	C519	5mm Fuses
230	C515	5mm Fuses
233	GMC	5mm Fuses
235	GMA	5mm Fuses
239	GMD	5mm Fuses
251	MCRW	Subminiature Fuses
257 / ATO	ATC	Blade Fuses
297 / MINI	ATM	Blade Fuses
299 / MAXI	MAX	Blade Fuses
312	AGC	¼" (6 x 32mm) Fuses
313	MDL	¼" (6 x 32mm) Fuses
314	ABC	¼" (6 x 32mm) Fuses
315	MDL-V	¼" (6 x 32mm) Fuses
318	AGC-V	¼" (6 x 32mm) Fuses
322	GBB	¼" (6 x 32mm) Fuses
324	ABC-V	¼" (6 x 32mm) Fuses

Littelfuse	Cooper Bussmann	Description
325	MDA-V	¼" (6 x 32mm) Fuses
326	MDA	¼" (6 x 32mm) Fuses
372	SR-5	Micro Fuses
373	SR-5F	Micro Fuses
382	SR-5H	Micro Fuses
392	SS-5	Micro Fuses
395	SS-5F	Micro Fuses
433	3216FF-R	Chip Fuses
434	0603FA-R	Chip Fuses
448	6125FF-R	Brick Fuses
451	6125FF-R	Brick Fuses
452	6125TD-R	Brick Fuses
453	6125FF-R	Brick Fuses
454	6125TD-R	Brick Fuses
459	6125FF-R	Brick Fuses
460	6125TD-R	Brick Fuses
461	TCP-R	Brick Fuses
464	1025FA-R	SMD Fuses
465	1025TD-R	SMD Fuses
466	3216FF-R	Chip Fuses
467	0603FA-R	Chip Fuses
468	3216TD-R	Chip Fuses
473	MCRS	Subminiature Fuses
PGB1010603	0603ESDA-TR1	ESD Suppressors

Order samples online - [www.cooperbussmann.com](http://www.cooperbussmann.com)

© 2008 Cooper Bussmann  
 St. Louis, MO 63178  
 636-394-2877  
[www.cooperbussmann.com](http://www.cooperbussmann.com)

