

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190730237](#)
Status: **Active**
Overview: Solderless Terminals
Description: Avikrimp Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 3/8" (M9), Length 34.59mm, Mylar Tape Carrier

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-015-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Ring and Spade Terminals
 Series [19073](#)
 Crimp Quality Equipment Yes
 Overview [Solderless Terminals](#)
 Product Name Avikrimp
 Type Ring
 UPC 800753077850

Physical

Barrel Type Closed
 Flammability 94V-2
 Insulation Nylon (PA)
 Material - Plating Mating Tin
 Net Weight 2.763/g
 Packaging Type Adhesive Tape on Reel
 Stud Size 3/8" (M9)
 Wire Insulation Diameter 5.72mm max.
 Wire Size AWG 10, 12
 Wire Size mm² 3.30-5.00

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number C-840-38T

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-015-001
 Sales Drawing SD-19073-008



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/88/2018 (15
 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19073 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Perishable Tooling Spacers for tape product	190270133
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	192880179
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press Mini-Mac Applicator	192880502 638851500

This document was generated on 09/20/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION