

Material Safety Data Sheet Quick Braid

1. IDENTIFICATION OF THE SUBSTANCE / PREPARATION AND OF THE COMPANY / UNDERTAKING.

| | | |
|-----|--|--|
| 1.1 | Identification of substance (as per label): Other means of Identification: | Quick Braid Desoldering Braid |
| 1.2 | Company Name: Easy Braid Co. Contact Name: James Strempe Full Address: 11543 K-tel Drive Minneapolis, MN 55343 Telephone Number: 952-929-3040 Fax Number: 952-929-2765 Emergency Number: | Part Numbers: Q-A-5, Q-A-5AS, Q-A-10, Q-A-10AS, Q-A-25, Q-A-25AS, Q-A-50, Q-A-50AS, Q-A-100, Q-A-100AS, Q-A-500, Q-A-500AS, Q-B-5, Q-B-5AS, Q-B-10, Q-B-10AS, Q-B-25, Q-B-25AS, Q-B-50, Q-B-50AS, Q-B-100, Q-B-100AS, Q-B-500, Q-B-500AS, Q-C-5, Q-C-5AS, Q-C-10, Q-C-10AS, Q-C-25, Q-C-25AS, Q-C-50, Q-C-50AS, Q-C-100, Q-C-100AS, Q-C-500, Q-C-500AS, Q-D-5, Q-D-5AS, Q-D-10, Q-D-10AS, Q-D-25, Q-D-25AS, Q-D-50, Q-D-50AS, Q-D-100, Q-D-100AS, Q-D-500, Q-D-500AS, Q-E-5, Q-E-5AS, Q-E-10, Q-E-10AS, Q-E-25, Q-E-25AS, Q-E-50, Q-E-50AS, Q-E-100, Q-E-100AS, Q-E-500, Q-E-500AS |

2. COMPOSITION / IDENTIFICATION ON INGREDIENTS

| CAS NUMBER | INGREDIENTS | % | SYMBOLS | RISK PHASE |
|------------|-------------------|------|---------|------------|
| 7440-50-8 | Pure Copper Metal | 99.9 | | |
| 8050-09-7 | Modified Rosin | .1% | | |

| | | |
|-----|---|--|
| 2.1 | Substances presenting a health hazard: | The 0.1% Rosin may cause allergic reactions: does not contain hazardous ingredients. |
| 2.2 | Exposure Limit Values: | Copper - ACGIH TLV |
| 2.3 | Is substance is confidential - indicate chemical nature to ensure safe handling | -fume 0.1mg/m3 -dust 1.0mg/m3 |

3. HAZARDS IDENTIFICATION

| | | |
|-----|--|--|
| 3.1 | Critical Hazards: | HMIS Hazard Rating: 0 = insignificant 1 = slight 2 = moderate 3 = high 4 = extreme |
| 3.2 | Critical Hazards to Man & Environment: | Health = 1 Flammability = 0 Reactivity = 0 Rosin flux may cause an allergic reaction, resulting in a skin rash. Clean hands after use. |
| | Adverse Human Health Effects and Symptoms: | |

4. FIRST AID MEASURE

| | | |
|-----|---|--|
| 4.1 | <u>Skin Contact:</u> -First Aid: -Symptoms: -Effects: -Delayed Effects: -Medical Attention Needed: <u>Eye Contact:</u> -First Aid: -Symptoms: -Effects: -Delayed Effects: -Professional Attention Needed: <u>Inhalation:</u> -First Aid: -Symptoms: -Effects: -Delayed Effects: -Professional Attention Needed: <u>Ingestion:</u> -First Aid: -Symptoms: -Effects: -Delayed Effects: -Professional Attention Needed: | Flush skin with copious amounts of water. Rash. Remove metal fragments and flush eyes with water. Remove to fresh air. If breathing has stopped, administer CPR. Induce vomiting. Wire strands could cause internal digestive tract bleeding. Induce vomiting. |
|-----|---|--|

5. FIRE FIGHTING MEASURES

| | | |
|-----|---|--|
| 5.1 | Suitable Extinguishing Media: | Powder Dolomite, Sodium Chloride or Graphite. |
| 5.2 | Unsuitable Extinguishing Media: | Do not use water. |
| 5.3 | Exposure Hazards: | Copper reacts violently with C ₂ H ₂ , NH ₄ N ₃ , Bromates, Chlorates, Iodates, C ₁₂ , C ₁ F ₂ , Ethylene Oxide, F ₂ , H ₂ O ₂ , Hydrazine monoitrate, Hydrazoic acid, H ₂ S, K ₂ O ₂ , NaN ₃ , Na ₂ O ₂ , CUN ₃ , S. |
| 5.4 | Combustion Products: -Resulting Gases: | Carbon Monoxide, Aliphatic Aldehydes, and Acids |
| 5.5 | Protective Equipment For Firefighters: | Not Needed |

6. ACCIDENTAL RELEASE MEASURES

| | | |
|-----|---|--|
| 6.1 | <u>Personal Precautions:</u> -Ignition sources? -Provision for sufficient ventilation? -Control of dust? -Prevention of skin contact? -Prevention of eye contact? <u>Environmental Precautions:</u> | When subjected to temperatures over 180 ⁰ F, flux fumes should be vented. See Section 8.1. Vacuum or sweep up and dispose of as a non-cumbustable metal. Gloves not normally required. When clipping short lengths, protective eyewear is recommended. |
| 6.2 | Methods for Cleaning Up: | |
| 6.3 | Materials not to be Used for Cleaning Up: | |
| 6.4 | | Vacuum or sweep up and dispose of as a noncombustible solid. See above. See section 5, of this document. |

7. HANDLING & STORAGE

| | | |
|-----|---|---|
| 7.1 | Handling -General Rules -Technical Precautions for Safe Handling -Measures necessary to prevent airborne levels of chemical being generated as a result of handling. Recommended Storage Conditions | Store in cool, dry environment for functional purposes. None required. If product is exposed to temperatures are above 180 ⁰ F, use local ventilation. |
| 7.2 | -List incompatible materials -Quantity Limits for storage -Special Requirements for proper storage of chemical | See sections 5 & 2 of this document. |

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

| | | |
|-----|--|---|
| 8.1 | System Design (e.g. Fume Hoods, Ventilated Cabinets, Enclosure) | General mechanical or local hood. Ventilation is recommended for applications where the product will exceed 180 ⁰ F. |
| 8.2 | Control Parameters -Limit values or biological standards: Recommended Monitoring Procedures: | See Section 5, of this document. |
| 8.3 | Personal Protection | Use local or general ventilation away from the operator if the product |
| 8.4 | -Respiratory Protection: -Hand Protection: -Eye Protection: -Skin Protection: | temperature is exposed to 180 ⁰ F+. Gloves may be used if resin is a skin irritant. Eye protection should be worn when clipping short lengths. See hand protection. |
| 8.5 | CEN standards | Carcinogens < 0.1% |

9. PHYSICAL AND CHEMICAL PROPERTIES

| | | |
|------|---|---|
| 9.1 | Appearance: | Copper metallic braid with fine crystalline resin layer. |
| 9.2 | Odor: | None. |
| 9.3 | pH: | N/A |
| 9.4 | Boiling Point: | 1981 degrees F |
| 9.5 | Melting Point: | 1949 degrees F |
| 9.6 | Flash Point: | No flash |
| 9.7 | Flammability (solid gas): | None |
| 9.8 | Autoflammability: | None |
| 9.9 | Explosive Properties: | None |
| 9.10 | Oxidizing Properties: | Copper can oxidize if prolonged exposure in moist conditions. |
| 9.11 | Vapor Pressure: | N/A |
| 9.12 | Relative Density: | N/A |
| 9.13 | Solubility: | |
| | -Water Solubility | Negligible |
| | -Fat Solubility | Unknown |
| | Partition coefficient, n-octanol/water: | |
| 9.14 | Other Data: | |
| 9.15 | -Safety Parameters | N/A |
| | -Vapor Density | N/A |
| | -Miscibility | N/A |
| | -Evaporation rate | N/A |
| | -Conductivity | Copper is very conductive. |
| | -Viscosity | A solid |

10. STABILITY AND REACTIVITY

| | | |
|------|---|---|
| 10.1 | Stability | Stable |
| 10.2 | Conditions to avoid | |
| | -Effects | |
| 10.3 | Materials to Avoid | |
| | -Effects | |
| 10.4 | Hazardous Decomposition products | |
| | -the need for and the presence of stabilizers: | |
| | -hazardous exothermic reaction: | |
| | -change in appearance in the substance: | |
| | -hazardous products formed upon contact with water: | |
| | -possible degradation to unstable products: | |
| | | Hazardous environment can occur in the presence of excessive heat and/or chemicals as listed in Section 5, this document. |

11. TOXICOLOGICAL INFORMATION

| | | |
|------|--------------------------|--|
| 11.1 | Skin Exposure: | |
| | -Symptoms: | |
| | -Immediate Effects: | Possible allergic rash reaction. See Section 4, this document. |
| | -Delayed Effects: | |
| | -Chronic Effects: | |
| | -Special Health Effects: | |
| 11.2 | Eye Contact: | |
| | -Symptoms: | |
| | -Immediate Effects: | Possible danger of metal fragments. See Section 4, this document. |
| | -Delayed Effects: | |
| | -Chronic Effects: | |
| 11.3 | -Special Health Effects: | |
| | Inhalation: | |
| | -Symptoms: | |
| | -Immediate Effects: | If product is exposed to temperatures in excess of 180 ⁰ F, local ventilation must be used. |
| | -Delayed Effects: | |
| | -Chronic Effects: | |
| | -Special Health Effects: | |
| 11.4 | Ingestion: | |
| | -Symptoms: | |
| | -Immediate Effects: | May be moderately irritating to stomach lining. Induce vomiting if conscious. |
| | -Delayed Effects: | |
| | -Chronic Effects: | |
| | -Special Health Effects: | |

12. ECOLOGICAL INFORMATION

| | | |
|------|--|-----------------|
| 12.1 | Mobility -distribution to environmental compartments -surface tension -absorption / desorption -physical & chemical properties | Not applicable. |
| 12.2 | Degradability -biotic and abiotic degradation -aerobic and anaerobic degradation -persistence | Not applicable. |
| 12.3 | Accumulation -bioaccumulation potential -biomagnification | Not applicable. |
| 12.4 | Short and Long Term Effects on: - <i>Ecotoxicity</i> -aquatic organisms -soil organisms -plants and terrestrial animals - <i>Other Adverse Effects</i> -ozone depletion potential -photochemical ozone creation potential -effects on waste water treatment plants | Not applicable. |

13. DISPOSAL CONSIDERATIONS

| | | |
|------|---------------------|---|
| 13.1 | Safe Handling | Consult with local regulatory bodies to metallic solid waste disposal |
| 13.2 | Methods of Disposal | |

14. TRANSPORT INFORMATION

| | | |
|------|---|---|
| 14.1 | UN Number: | |
| 14.2 | Road & Sea Freight Classification: | Harmonized Tariff Code: #7413.00.1000 |
| 14.3 | Substance Classification Number: | |
| 14.4 | Class: | |
| 14.5 | Packing Group: | |
| 14.6 | Proper Shipping Name: PGR (if applicable) | Copper wire coated with resin flux |
| 14.7 | ADR/RID CLASSIFICATION: Class: | Validated license # / General license symbol: "NLR" |
| | Item Number: | |
| 14.8 | ICAO/IATA CLASSIFICATION: Class: Sub-Risk: Packing Group: Proper Shipping Name: | |

15. REGULATORY INFORMATION

| | | |
|------|---|---|
| 15.1 | -Toxic Substances Control Act (TSCA) -CERCLA/Superfund, 40 CFR 112, 302 -SARA Superfund and re-authorization Act of 1986 Sec 302 Sec 311/312 Sec 313 | All ingredients of this product are listed on the TSCA Inventory. None of the chemicals are Superfund hazards None of the chemicals are Section 302 hazards This product is non-hazardous None of the chemicals are Section 313 hazards |
|------|---|---|

16. OTHER INFORMATION

| | | |
|------|-------------------------|--|
| 16.1 | Regulatory Information: | |
|------|-------------------------|--|