

C0510X5R1A474M030AC

TDK Item Description : C0510X5R1A474MT****




Application & Main Feature

Commercial Grade (Low ESL Reverse Geometry)

Series

C0510 [EIA 0204]



Dimensions

L	0.52mm +/-0.05mm
W	1.00mm +/-0.05mm
T	0.30mm +/-0.05mm
B	0.10mm Min.

Temperature Characteristic

X5R (-55 to 85 degC +/-15%)

Rated Voltage

1A (10Vdc)

Capacitance

470nF

Capacitance Tolerance

M (+/-20%)

Dissipation Factor

10% Max.


Insulation Resistance

212Mohm Min.


AEC-Q200

Not Applicable


|Z|, ESR vs. Freq. Characteristics




Cap. vs. Freq. Characteristic



DC Bias Characteristic



Temperature Characteristics



Ripple Temperature Rise Characteristics

